


# FineAdjust Applicator Specification Sheet Order No. 63900-0100



### **FEATURES**

- Directly adapts to most automatic wire processing machines
- Quick punch removal with the push of a button for fast and easy tooling change
- Applicator designed to industry standard mounting and shut height 135.80mm (5.346")
- Quick set-up time; plus the crimp height, track and feed adjustments can be set without removing the applicator from the press
- Fine adjustment allows users to achieve target with little effort by adjusting in increments of .015mm (.0006") for conductor crimp height and .063mm (.0025") for insulation height
- Independent adjustment rings allow users to quickly adjust the conductor or insulation crimp height without affecting each other


### **SCOPE**

Products: 2.50mm (.098") Pitch Splash Proof Crimp Terminal, 20-22 AWG.

Terminal Series No.	Terminal Order No.	Wire Size		◆Insulatio	n Diameter	Strip Length	
		AWG	mm²	mm	ln.	mm	ln.
50038	50038-8000	20-22	0.50-0.35	1.50-1.90	.059-075	2.00-2.50	.078098
50039	50039-8000	20-22	0.50-0.35	1.50-1.90	.059-075	2.00-2.50	.078098

♦ Note:

Insulation OD: 1.50-1.70mm (.059-.067") will achieve optimum IPC-A620 class 2 insulation crimps. Insulation OD: 1.70-1.90mm (.067-.075") will not achieve optimum IPC-A620 class 2 insulation crimps.



The above terminal drawing is a generic terminal representation. It is not an image of a terminal listed in the scope.

Doc No: ATS-639000100 Release Date: 05-22-08 **UNCONTROLLED COPY** Page 1 of 5 Revision: A Revision Date: 05-22-08

### **CRIMP SPECIFICATION**

Terminal Series No.	Bell n	nouth	Cut-off Tak	Maximum	Conductor Brush	
	mm	ln.	mm	ln.	mm	ln.
50038	0.00-0.30	.000012	0.30	.012	0.10-0.90	.004035
50039	0.00-0.30	.000012	0.30	.012	0.10-0.90	.004035

	Bend up Bend down		Twist Roll		Punch Width mm (Ref)				Seam
Terminal Series No.					Cond	Conductor		ation	
	Degree (Max)		Degree (Max)		mm	In	mm	In	Seam shall not be open
50038	2	0	3	10	1.40	.055	1.80	.070	and no wire allowed out
50039	2	0	3	10	1.40	.055	1.80	.070	of the crimping area

After crimping, the conductor profile should measure the following.

Terminal Series No.	Wire Size		Conductor C	Crimp Height	<b>Pull Force Minimum</b>		
Terminal Series No.	AWG	mm <sup>2</sup>	mm	ln.	N	Lb.	
50038	20	0.50	0.96-1.06	.038042	53.3	12.0	
	22	0.35	0.94-0.99	.037039	48.9	11.0	
50039	20	0.50	0.96-1.06	.038042	53.3	12.0	
30039	22	0.35	0.94-0.99	.037039	48.9	11.0	

Pull Force should be measured with no influence from the insulation crimp.


The above specifications are guidelines to an optimum crimp.

Doc No: ATS-639000100 Release Date: 05-22-08 **UNCONTROLLED COPY** Page 2 of 5 Revision: A Revision Date: 05-22-08

## **PARTS LIST**

FineAdjust Applicator 63900-0100								
Item	Order No	Engineering No.	Description	Quantity				
Perishable Tooling								
	63900-0170	63900-0170	Tool Kit (All "Y" Items)	REF				
1	63444-1407	63444-1407	Conductor Punch	1 Y				
2	63445-1426	63445-1426	Conductor Anvil	1 Y				
3	63446-1808	63446-1808	Insulation Punch	1 Y				
4	63445-1810	63445-1810	Insulation Anvil	1 Y				
5	63443-0002	63443-0002	Cut-Off Plunger	1 Y				
6	63443-0012	63443-0012	Front Plunger Retainer	1 Y				
Other Components (000150)								
7	11-17-0022	1739-21	Hold Down Spring	1				
8	11-18-4083	60707-8	Feed Guide	1				
9	11-24-1067	4996-4	Cut-off Plunger Spring	1				
10	11-24-1149	4996-37	Shank	1				
11	11-40-4039	8302-5	Front Plunger Striker	1				
12	63443-0009	63443-0009	Scrape Chute	1				
13	63443-0025	63443-0025	Lower Tooling Key	1				
14	63443-0090	63443-0090	Wire Stop	1				
15	63443-1719	63443-1719	18.90mm Height Spacer	1				
16	63443-2213	63443-2213	13.00mm Coarse Spacer	1				
17	63443-2302	63443-2302	3.10mm Spacer	1				
18	63443-2314	63443-2314	3.70mm Fine Spacer	1				
19	63443-6111	63443-6111	Rear Cover	1				
20	63443-7001	63443-7001	Terminal Hold Down	1				
Frame								
21	63800-4901	63800-4901	Тор	1				
22	63801-3281	63801-3281	Base	1				
23	63801-4650	63801-4650	Track	1				
		Н	lardware					
24	N/A	N/A	M3 by 6 Long SHCS	2**				
25	N/A	N/A	M3 by 6 Long FHCS	1**				
26	N/A	N/A	M4 by 6 Long SHCS	2**				
27	N/A	N/A	M4 by 12 Long BHCS	2**				
28	N/A	N/A	M5 by 12 Long SHCS	1**				
29	N/A	N/A	M4 by 50 Long SHCS	2**				
30	N/A	N/A	#5-40 by 3/8 Long SHCS	1**				
31	N/A	N/A	#10-32 by 3/8"Long Flat Point SSS	1**				
32	N/A	N/A	#10-32 Hex Jam Nut	1**				
*	** Available from an industrial supply company such as MSC (1-800-645-7270).							

Doc No: ATS-639000100 Release Date: 05-22-08 **UNCONTROLLED COPY**Revision: A Revision Date: 05-22-08



Doc No: ATS-639000100 Revision: A Release Date: 05-22-08 Revision Date: 05-22-08

### NOTES

- 1. Molex recommends an extra perishable tooling kit be maintained at your facility.
- 2. Verify tooling alignment by manually cycling the press and Applicator before crimping under power. Check that all screws are tight.
- 3. Slugs, Terminals, Dirt and Oil should be kept clear of work area.
- 4. Wear safety glasses at all times.
- 5. For recommended maintenance refer to the FineAdjust Manual.

CAUTION: This applicator should only be used in a press with a shut height of 135.8mm (5.346"). Tooling damage could result at a lower setting.

**CAUTION**: To prevent injury never operate this Applicator without the guards supplied with the press or wire-processing machine in place. Reference the press or wire processing manufacturer's instruction manual.

CAUTION: Molex crimp specifications are valid only when used with Molex terminals, applicators and tooling.

Americas Headquarters Lisle, Illinois 60532 U.S.A. 1-800-78MOLEX amerinfo@molex.com

Far East North Headquarters Far East South Headquarters European Headquarters Corporate Headquarters Yamato, Kanagawa, Japan 81-462-65-2324 feninfo@molex.com

Jurong, Singapore 65-6-268-6868 fesinfo@molex.com

Munich, Germany 49-89-413092-0 eurinfo@molex.com

2222 Wellington Ct. Lisle, IL 60532 U.S.A. 630-969-4550 Fax: 630-969-1352

Visit our Web site at http://www.molex.com

**UNCONTROLLED COPY** Doc No: ATS-639000100 Release Date: 05-22-08 Page 5 of 5 Revision: A Revision Date: 05-22-08